



BITO4, Opposite Side Two Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BITO4](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 2
Sided Entry, 14-4 AWG, Al/Cu Rated, 1.16 IN L.



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	BITO4
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	1/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	90°C
Trade Name	UNITAP™
Type	BIT
UPC	781810134139
UPC 12 Digit	7818101341399

Dimensions

Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	27.44 mm
Dimension - Length Overall inch	1.08 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	14 AWG - 4 AWG
Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Size	14-4 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - BITO4_MODEL-PDF](#)
[3D Models - BITO4_MODEL-IGES](#)
[3D Models - BITO4_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIT_Lineart](#)
[Sales Drawings - sc210991-02](#)
[Specifications - BITO4](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BITO4-SPEC-EN | REV 8/2024