

BIBS2/06MT, Single Sided Mounted Six Conductor Clear Insulated Multi-Tap Connector

By Burndy

Catalog # [BIBS2/06MT](#)

Aluminum Multiple Tap Connector w/ Mount Holes, Clear Insulated, 6 Port, 1 Sided Entry, 14-2/0 AWG, Al/Cu Rated.



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Catalog Number	BIBS2/06MT
Connector Type	Multi Tap
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	6
Physical Attribute - Number of Screws	8
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810252772
UPC 12 Digit	7818102527722

Dimensions

Dimension - Height inch	1.50 in
Dimension - Height mm	38.1 mm
Dimension - L Length Overall mm	141 mm
Dimension - Length Overall inch	5.54 in
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIBS-MT_LineArt](#)
[Sales Drawings - 213079](#)
[Specifications - BURNDY_BIBS206MT_Specsheet](#)
[Specifications - BIBS2/06MT](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBS206MT-SPEC-EN | REV 10/2024