



BIBS35012FX, Single Sided Flex Rated Twelve Conductor Clear Insulated Mult-Tap Connector

By Burndy
Catalog # [BIBS35012FX](#)

Aluminum UNITAP, Single Sided Entry, #10-350 Class B & C ,#10-250 Class G,H,I,K, DLO, 12 PORT.



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBS35012FX
Color Code	Red
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	12
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945439689
UPC 12 Digit	6219454396899

Dimensions

Dimension - Height inch	2.5 in
Dimension - L Length Overall mm	281.18 mm
Dimension - Length Overall inch	11.07 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper DLO Size	10 - 250 Str Range
Conductor - Copper Flex G Size	10 - 250 Str Range
Conductor - Copper Flex H Size	10 - 250 Str Range
Conductor - Copper Flex I Size	10 - 250 Str Range
Conductor - Copper Flex K Size	10 - 250 Str Range
Conductor - Copper Str Size	10 AWG - 350 kcmil Range
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Fex-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50046931](#)
- [Specifications - BIBS35012FX](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBS35012FX-SPEC-EN | REV 8/2024