



C11N, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube

By Burndy
Catalog # C11N

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2"- 1" Water Pipe, pipe clamp:50 in-lb.



Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

General

Catalog Number	C11N
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware Plated	Zinc Plated Steel
Plating Type	N
Sub Brand	Unplated
Type	CLAMP
UPC	Ground Clamp
UPC 12 Digit	781810142288

Dimensions

Dimension - Height inch	1.81 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.25 in
Dimension - Pad Width inch	0.63 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

3D Models - C11N_MODEL-IGES

3D Models - C11N_MODEL-PDF

3D Models - C11N_MODEL-STEP

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_CN_LineArt

Sales Drawings - sc210654-01

Specifications - C11N



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-C11N-SPEC-EN | REV 8/2024