



## C22D, Cast Bronze Ground Clamp, Cable to Pipe or Tube

By Burndy  
Catalog # C22D

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1-1/4" - 2" Water Pipe.



### Application

For Connecting Grounding Conductor To Water Pipe Or Copper Tube, Direct Burial Applications In Earth And Concrete

### General

Catalog Number	C22D
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze
Plating Type	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810142356
UPC 12 Digit	7818101423566

### Dimensions

Dimension - Height inch	2.38 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.63 in
Dimension - Pad Width inch	1.00 in
Dimension - Width inch	0.75 in
Dimension - Width mm	19 mm

### Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size Range	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size Range	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 in-2 in

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

3D Models - C22D\_MODEL-IGES

3D Models - C22D\_MODEL-STEP

3D Models - C22D\_MODEL-PDF

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR\_CN\_LineArt

Sales Drawings - sc210654-01

Specifications - C22D



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-C22D-SPEC-EN | REV 8/2024