



BIT2/OFX, Single Sided Flex Rated Two Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIT2/OFX](#)

Aluminum UNITAP, Tap - Same Side Entry, #14-2/0 Class B & C,
#14-#1 Class G,H,I,K, DLO, 2 PORT



Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Application

Clear Insulated Multiple Tap Connectors

General

Catalog Number	BIT2/0FX
Color Code	Black
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16 in
Installation Torque	14-6 Str- 80 in-lb, 4- 2/0 Str -
Recommended in-lb	100 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135 °C
Trade Name	UNITAP™
Type	BIT, UNITAP
UPC	621945439207
UPC 12 Digit	6219454392077

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.52 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33.27 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper DLO Size Range	14 - 1 Str
Conductor - Copper Flex G Size Range	14 - 1 Str
Conductor - Copper Flex H Size Range	14 - 1 Str
Conductor - Copper Flex I Size Range	14 - 1 Str
Conductor - Copper Flex K Size Range	14 - 1 Str
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BIT2/0FX](#)
[Specifications - Burndy_BIT20FX_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIT20FX-SPEC-EN | REV 8/2024