



# C4JPT, Cast Bronze Clamp, Cable to Water Pipe

By Burndy  
Catalog # C4JPT

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG - 6 AWG, 2-1/2" - 4" Water Pipe, 1/2" Hub.

## Features

- Cast bronze clamp for conduit
- Pressure bar type conduit hub adjusts for 1/2", 3/4" EMT, or 1/2" rigid conduit
- Supplied with zinc plated hardware
- UL467 Listed for the US and Canadian markets

## General

Catalog Number	C4JPT
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
UPC	781810142271
UPC 14 Digit GTIN	00781810142271

## Dimensions

Dimension - Height inch	4.39 in
Dimension - Height mm	111.5 mm
Dimension - L Length Overall mm	131 mm
Dimension - Length Overall inch	5.15 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

## Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG

Conductor - Copper Str Size Range	8 AWG - 6 AWG
Conductor - Pipe EMT Size	2 1/2 in;3 in;3 1/2 in;4 in
Conductor - Pipe EMT Size Range	2 1/2 in-4 in
Conductor Type	<ul style="list-style-type: none"><li>• Pipe EMT-Size</li><li>• CU C Solid-Size</li></ul>

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	NC
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CJPT\\_LineArt](#)
- [Sales Drawings - sc210672-01](#)
- [Specifications - C4JPT](#)