



BIT350FX, Single Sided Flex Rated Two Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIT350FX](#)

Aluminum UNITAP, Tap - Same Side Entry, #10-350 Class B & C,
#10-250 Class G,H,I,K, DLO, 2 PORT



Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Application

Clear Insulated Multiple Tap Connectors

General

Catalog Number	BIT350FX
Color Code	Red
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16 in
Installation Torque	310 in-lb
Recommended in-lb	
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135 °C
Trade Name	UNITAP™
Type	BIT, UNITAP
UPC	621945440029
UPC 12 Digit	6219454400299

Dimensions

Dimension - Height inch	2.5 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.22 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60.45 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper DLO Size Range	10 - 250 Str
Conductor - Copper Flex G Size Range	10 - 250 Str
Conductor - Copper Flex H Size Range	10 - 250 Str
Conductor - Copper Flex I Size Range	10 - 250 Str
Conductor - Copper Flex K Size Range	10 - 250 Str
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BIT350FX](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIT350FX-SPEC-EN | REV 8/2024