



BITO2/OFX, Opposite Side Flex Rated Two Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BITO2/OFX](#)

Insulated tap offset ports flex conductor rated, Wire size: 2/0,
Color: Black, Amp Rating : 175.



Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Application

Clear Insulated Multiple Tap Connectors

General

Catalog Number	BITO2/0FX
Color Code	Black
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16 in
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNITAP
Temperature Rating	135°C
Trade Name	UNITAP™
Type	BIT, UNITAP
UPC	621945440647
UPC 12 Digit	6219454406477

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	38.61 mm
Dimension - Length Overall inch	1.52 in
Dimension - Width inch	1.56 in
Dimension - Width mm	39.62 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper DLO Size Range	14 str.-1 str.
Conductor - Copper Flex G Size Range	14 str.-1 str.
Conductor - Copper Flex H Size Range	14 str.-1 str.
Conductor - Copper Flex I Size Range	14 str.-1 str.
Conductor - Copper Flex K Size Range	14 str.-1 str.
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BITO2/0FX](#)
[Specifications - Burndy_BITO20FX_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BITO20FX-SPEC-EN | REV 8/2024