



C11CSH1, Cast Bronze Clamp with Copper Strap, Cable to Water Pipe

By Burndy
Catalog # C11CSH1



Cast Bronze Clamp with Copper Strap, Cable to Water Pipe, 6 AWG (Sol.), 1/2" - 1" Water Pipe, 1/2" hub.

Application

For Grounding Rigid Conduit Systems

General

Catalog Number	C11CSH1
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware Plated	Zinc Plated Steel N
Plating Type	Zinc
Sub Brand	CLAMP
Type	WaterPipe Grounding Connectors
UPC	781810142479
UPC 12 Digit	7818101424799

Dimensions

Dimension - D inch	6.12 in
Dimension - Height inch	1.75 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.50 in
Dimension - Pad Width inch	1.06 in
Dimension - Width inch	1.06 in
Dimension - Width mm	27 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	8 SOL. - 4 SOL.
Conductor - Copper Solid Size Range	8 SOL. - 4 SOL.
Conductor - Copper Str Size	8 STR. - 4 STR.
Conductor - Copper Str Size Range	8 AWG - 4 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - C11CSH1_MODEL-IGES](#)
- [3D Models - C11CSH1_MODEL-STEP](#)
- [3D Models - C11CSH1_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_C11CSH_LineArt](#)
- [Sales Drawings - SC..210666-01](#)
- [Specifications - C11CSH1](#)



A Hubbell brand