



# C11K17D, Cast Bronze Ground Clamp with Lay-in Feature, for Water Pipe, Rebar, Ground Rod, to Tap Conductor

By Burndy  
Catalog # [C11K17D](#)

Cast Bronze Ground Clamp w/Lay-in Feature, 1/2"-1" Water Pipe, #4-#6 Rebar, 3/8"-1" Ground Rod (Main), #10 Sol-#2 Str Ground, Silicon Bronze H/W.

## Features

- Lay-In Feature
- Connects Grounding Conductor to Water Pipe, Copper Tube, Ground Rod or Rebar
- Open face design allows for a fast lay-in on the tap conductor without need for cutting
- Reverse bottom clamp for smaller size, rebar or rod

## Application

For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar And Direct Burial

## General

Catalog Number	C11K17D
Construction Material - Main	Cast Bronze Body
EU RoHS Indicator	Yes
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810358634
UPC 14 Digit GTIN	00781810358634

## Dimensions

Dimension - Height inch	1.64 in
Dimension - Height mm	41.7 mm
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.28 in
Dimension - Width inch	0.66 in
Dimension - Width mm	17 mm

## Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3
-----------------------------	--



Conductor - Copper Str Size Range	AWG;2 AWG 10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Rebar Size	4 ;5 ;6
Conductor - Rebar Size Range	4 -6
Conductor - Rod Size	3/8 in;1/2 in;5/8 in;3/4 in;7/8 in;1 in
Conductor - Rod Size Range	3/8 in-1 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Burndy Grounding Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_C11K16D\\_LineArt](#)  
[Sales Drawings - 10037614-01\\_B](#)



A Hubbell brand