



C8, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube

By Burndy
Catalog # [C8](#)

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper
Tube, 10 - 2 AWG, 4-1/2" - 6" Water Pipe.

Features

- Connects grounding conductor to water pipe or copper tube
- Supplied with Zinc-plated steel hardware

Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe
Or Copper Tube

General


Catalog Number	C8
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Trade Name	N
Type	Ground Clamp
UPC	781810142332
UPC 14 Digit GTIN	00781810142332

Dimensions

Dimension - Height inch	4.29 in
Dimension - Height mm	109 mm
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	212 mm
Dimension - Length Overall inch	8.34 in
Dimension - Pad Width inch	1.88 in
Dimension - Thread Size	-
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Conductor Related

Conductor - Armored Cable Size	N
--------------------------------	---



Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	4 in
Conductor - Pipe EMT Size Range	4 in
Conductor - Rebar Size Range	N/A

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	N
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CN_LineArt](#)
[Sales Drawings - sc210654-01](#)
[Specifications - C8](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-C8-SPEC-EN | REV 3/2025