

CP32A32A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # CP32A32A



ACSR,6201,5005: 203.2,336.4,397.5 CU. & ALUM.: 397.5,400 GROOVE A GROOVE B.

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

General

Catalog Number	CP32A32A
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012987
UPC 12 Digit	7818100129877

Dimensions

Dimension - B Length inch	5 in
Dimension - Height fraction	3 in
Dimension - Height inch	3 in
Dimension - Width fraction	2-1/2 in
Dimension - Width inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	203.2 (16/9) Brahma kcmil-397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size A	397 kcmil;400 kcmil
Conductor - AL Str Size A Range	397 kcmil-400 kcmil
Conductor - AL Str Size B	397 kcmil;400 kcmil
Conductor - AL Str Size B Range	397 kcmil-400 kcmil
Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size A Range	400 kcmil
Conductor - Copper Str Size B	400 kcmil
Conductor - Copper Str Size B Range	400 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section H - Overhead

Distribution

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_CPA_CLAMP_LineArt

Sales Drawings - SD..028518-01

Specifications - CP32A32A



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-CP32A32A-SPEC-EN | REV 8/2024