



ES25A4W, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES25A4W](#)

SIDE A: 1/0STR AL-CU COLOR: YELLOW SIDE B: 6 ACSR,
5,6STR AL-CU, 4SOL AL-CU COLOR: BLUE.



Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

General

Catalog Number	ES25A4W
Color Code - Side A	Yellow
Color Code - Side B	Blue
Die Index	BG or 5/8
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810097977
UPC 12 Digit	7818100979777

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B	6 AWG;5 AWG
Conductor - AL Str Size B Range	6 AWG-5 AWG
Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Str Size B	6 AWG;5 AWG
Conductor - Copper Str Size B Range	6 AWG-5 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_ES_Insulink_lineart](#)
[Sales Drawings - 50115706](#)
[Specifications - ES25A4W](#)