

GD1529, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy

Catalog # [GD1529](#)



Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 200 kcmil, 1-1/8" to 1-1/4" Rod, 1" Pipe, DURIUM #6 (U-Bolt), Hex Nuts & SPLW.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

General

Catalog Number	GD1529
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	244
UPC	781810260265
UPC 14 Digit GTIN	00781810260265

Dimensions

Dimension - B Length inch	1.13 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.38 in
Dimension - Height mm	85.9 mm
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	1
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	1-1/8;1-1/4

Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor - Rod Size	1 1/4 in
Conductor - Rod Size Range	1 1/4 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[3D Models - GD1529_MODEL-STEP](#)
[3D Models - GD1529_MODEL-PDF](#)
[3D Models - GD1529_MODEL-IGES](#)
[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_gdla](#)
[Sales Drawings - SD..013775-01](#)
[Specifications - GD1529](#)



A Hubbell brand