



# GSTUD34HY Structural Steel Ground Stud

By Burndy  
Catalog # [GSTUD34HY](#)

Structural Steel Grounding Connector; Accommodates: 4/0 AWG; 3/4" Rod; Copper Coated; Nickel Plated



## Features

- May be welded to steel surfaces quickly and easily
- No disk grinding needed
- Knurled surface for better gripping
- Copper plated
- May be installed during adverse weather conditions

## Application

- For Compression Connectors And Mechanical Connectors

## General

Catalog Number	GSTUD34HY
EU RoHS Indicator	Yes
Material	Steel
Plated	Y
Plating Type	Nickel
Sub Brand	HYGROUND, VERSITAIL
Trade Name	VERSITAIL™
Type	<ul style="list-style-type: none"> <li>• GSTUD-HY</li> <li>• GSTUD-HY</li> </ul>
UPC	781810220900
UPC 12 Digit	7818102209000

## Dimensions

Dimension - B Length fraction	19/25 in
Dimension - B Length inch	0.76 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	3/4 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.81 in
Physical Attribute - Tongue Angle	45 Degree

## Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	<ul style="list-style-type: none"> <li>• Rod-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	1960

## Product Assets

- [3D Models - GSTUD34HY\\_MODEL-PDF](#)
- [3D Models - GSTUD34HY\\_MODEL-IGES](#)
- [3D Models - GSTUD34HY\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_GSTU-HY\\_LineArt](#)
- [Sales Drawings - sd..086414-01](#)
- [Specifications - GSTUD34HY](#)



A Hubbell brand