



GAR1529W, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy

Catalog # [GAR1529W](#)



To Rod or Pipe with the Same Connector; Hot Tin Dipped.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

General

Catalog Number	GAR1529W
Installation Torque	240 Lb in
Recommended Run in-lb	
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin Plated bodies and electro tin plated hardware
U Bolt Type	244
UPC	781810079119
UPC 14 Digit GTIN	00781810079119

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	3.38 in
Dimension - Height mm	85.9 mm
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	250 Kcmil
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil

Conductor - Copper Tube Std Size	1
Conductor - Copper Tube Std Size Range	1
Conductor - Pipe or Round Tube Size Range	1 in
Conductor - Rebar Size	8;9
Conductor - Rebar Size Range	8-9
Conductor - Rod Size	1.120-1.31 in
Conductor - Rod Size Range	1 1/8-1 1/4
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)
[Sales Drawings - SD015789](#)
[Specifications - GAR1529W](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-GAR1529W-SPEC-EN | REV 3/2025