



## GD2229, Mechanical Grounding Connector, 2 Cables to Rod or Pipe

By Burndy

Catalog # [GD2229](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 4" to 4-1/2" Rod, 4" Pipe.

### Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

### Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

### General

Catalog Number	GD2229
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GD
U Bolt Type	261
UPC	781810238967
UPC 14 Digit GTIN	00781810238967

### Dimensions

Dimension - B Length inch	1.63 in
Dimension - Height fraction	6-3/8 in
Dimension - Height inch	6.38 in
Dimension - Height mm	162.1 mm
Dimension - Width fraction	5-7/8 in
Dimension - Width inch	5.81 in
Dimension - Width mm	148 mm

### Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	4



Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	4
Conductor - Copper Tube Std Size Range	4
Conductor Size	2/0 AWG Sol - 250 kcmil

### Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[3D Models - GD2229\\_MODEL-IGES](#)  
[3D Models - GD2229\\_MODEL-PDF](#)  
[3D Models - GD2229\\_MODEL-STEP](#)  
[Catalogs - Burndy Grounding Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_gdla](#)  
[Sales Drawings - SD..013775-01](#)  
[Specifications - GD2229](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-GD2229-SPEC-EN | REV 3/2025