

# GRC58, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy  
Catalog # [GRC58](#)



Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 1 AWG (Str), 5/8" Drive Rod, 3/8" Stud.

## Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

## Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete

## General

Catalog Number	GRC58
EU RoHS Indicator	Yes
Hardware Type	Silicon Bronze
Material	Copper Alloy
Material - Hardware	Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRC, High Strength
UPC	781810230961
UPC 12 Digit	7818102309611

## Dimensions

Dimension - B Length inch	0.57 in
Dimension - Height inch	2.18 in
Dimension - Height mm	55.6 mm
Dimension - Length Side B inch	0.63 in
Dimension - Width inch	0.95 in
Dimension - Width mm	24 mm

## Conductor Related

Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size Range	12 AWG-1 AWG
Conductor - Rod Size	5/8 in
Conductor Size	#10 AWG Sol - #1 AWG Str

## Conductor Type

- Rod-Size
- CU C Solid-Size

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	27500

## Product Assets

- [360 Product View - BURN\\_GRC58](#)
- [3D Models - GRC58\\_MODEL-PDF](#)
- [3D Models - GRC58\\_MODEL-IGES](#)
- [3D Models - GRC58\\_MODEL-STEP](#)
- [3D Product View - BURN\\_GRC58](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_GRC\\_Lineart](#)
- [Sales Drawings - SA..076868-01](#)