

# KA4CNK, CU Terminal, Nickel Plated; #14 Solid - #4 Stranded; 1/4" Stud; 45 in-lb recommended torque

By Burndy  
Catalog # [KA4CNK](#)



CU Terminal, Nickel Plated; #14 Solid - #4 Stranded; 1/4" Stud; 45 in-lb recommended torque.

## Features

- Compact, high copper alloy terminal for joining cable to equipment pads or terminal blocks
- Nickel plated

## General

Catalog Number	KA4CNK
Connector Type	Terminal
Hardware Type	5/16 UNF Slotted SetScrew
Installation Torque	45 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Nickel
Type	Bolted Lugs & Terminals
UPC	781810079881

## Dimensions

Dimension - B Length fraction	8/17 in
Dimension - B Length inch	0.47 in
Dimension - Height fraction	67/87 in
Dimension - Height inch	0.77 in
Dimension - Height mm	19.6 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.11 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.54 in

Dimension - Stud Size inch 1/4

## Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	59400

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SC088846-01\\_B](#)  
[Specifications - KA4CNK](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-KA4CNK-SPEC-EN | REV 10/2024