

KLU300TP, Mechanical Offset Tongue Terminal for Cu, 1/0 Str-350 kcmil, 3/8" Stud

By Burndy
Catalog # [KLU300TP](#)



SCRULUG™ Mechanical Offset Tongue Terminal for Copper Cable; 1-Hole; Accommodates: 1/0 Str - 350 kcmil; Stud: 3/8"; Hardware: 5/8" Hex Head; Installation Torque: 275 in-lbs; Wire Strip Length: 1-5/8".

Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

General

Catalog Number	KLU300TP
Connector Type	Pressure Bar
Hardware Type	5/8 UNF Socket/HexScrew
Installation Torque	275
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	621945467736

Dimensions

Dimension - B Length fraction	1-7/32 in
Dimension - B Length inch	1.22 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.83 in
Dimension - N inch	0.52 in
Dimension - Pad Width inch	0.99 in

Dimension - Screw Size inch	5/8
Dimension - Strip Length inch	1-5/8
Dimension - Stud Size inch	3/8

Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	1/0 -350 kcmil
Conductor Size	1/0 AWG-350 KCMIL
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Minimum Pack Quantity	10
Pallet Quantity	11600

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd207469-01](#)
- [Specifications - KLU300TP](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-KLU300TP-SPEC-EN | REV 10/2024