



KS26, Split Bolt Connector, Run/Tap: #2 AWG-2/0 AWG Str

By Burndy
Catalog # [KS26](#)



Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap).

Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	385
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810013281
UPC 12 Digit	7818100132811

Dimensions

Dimension - B Length fraction	9/10 in
Dimension - B Length inch	.90 in
Dimension - Cross Flats inch	1.05 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94
Dimension - Width fraction	41/50 in
Dimension - Width inch	0.82 in
Dimension - Width mm	21 mm
Width	0.82 in

Conductor Related

Conductor - Copper Solid Run	3/0 AWG
Conductor - Copper Solid Run Range	2 AWG-2/0 AWG
Conductor - Copper Solid Tap	3/0 AWG
Conductor - Copper Solid Tap Range	14 AWG-2/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 STR - 2/0 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	2 STR - 2/0 STR
Conductor - CopperWeld Solid Run	3/0
Conductor - CopperWeld Solid Run Range	3/0
Conductor - CopperWeld Solid Tap	3/0
Conductor - CopperWeld Solid Tap Range	3/0
Conductor - CopperWeld Str Run	7 #7
Conductor - CopperWeld Str Run Range	7 #7
Conductor - CopperWeld Str Tap	7 #7
Conductor - CopperWeld Str Tap Range	7 #7
Conductor - Rebar Size	3
Conductor - Rebar Size Range	3
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved No

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	8700

Product Assets

- [3D Models - KS26_MODEL-STEP](#)
- [3D Models - KS26_MODEL-IGES](#)
- [3D Models - KS26_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
- [Sales Drawings - SD..078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)



A proud member of the Hubbell Family.