

KK3A44U4N, AL Universal Terminal, 3 Conductor, 500-1000 kcmil, 4-Hole, 1/2" Stud, 1.75" Spacing, 6 Screws, Al/Cu Rated

By Burndy

Catalog # [KK3A44U4N](#)

Aluminum Universal Terminal, 3 Conductor, 4 Hole, 500-1000 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 6 Screws, Al/Cu Rated, Tin Plated.



Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy, electro tin-plated to provide low contact resistance

General

Catalog Number	KK3A44U4N
Connector Type	Parallel Set-Screw
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin Plated
Type	Bolted Lugs & Terminals
UPC	781810601075

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	1.90 in
Dimension - Height mm	48.3 mm
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.19 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	4.77 in
Dimension - Stud Size inch	0.56 in

Conductor Related

Conductor - AL Str Size	500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Size Range	500 - 1000 Kcmil
Conductor - Copper Str Size Range	500 - 1000 Kcmil
Conductor Size	500-1000 KCMIL
Conductor Type	<ul style="list-style-type: none"> CU C Str-Size AL C Str-Size
Number Of Wires	3
Number of Conductors	3

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KK3A-U_LineArt](#)
[Sales Drawings - se210997](#)



A Hubbell brand