



PATRIOT 12-Ton Covered C-Head Battery Crimper,C-Head, Hydraulic Self-Contained, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy
Catalog # [PAT750CL5PB](#)

PAT750 12T Covered C-Head Battery Crimper, 5Ah Li-ion, AC, Nylon Pro Bag.

Features

- C-Head with 1.65" jaw opening
- 355° head rotation
- Uses U dies
- Ergonomic design and overmolded handle for comfort grip
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

General

Application	Crimping
Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT750CL5PB
Container Type	Nylon Pro Bag
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561458
UPC 12 Digit	621945561458

Dimensions

Dimensions	15.75 in x 3.5 in x 13.50 in
Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	15.2 lb
Width	3.5 in



Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground Rod: 1/2" - 1" diameter
-----------------	--

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106125](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Video - PAT750 Series](#)
[Video - BURNDY Pro Bag, BURNDY Minute](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-PAT750CL5PB-SPEC-EN | REV 6/2024