



PATRIOT® IN-LINE® 6-Ton Scissor Action, BG/D3 Crimp Jaw, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Utility Bag

By Burndy
Catalog # [PATMD6LW](#)

PATMD-LW IN-LINE® 6T Scissor Action, BG/D3 Crimp Jaw, 3Ah Li-ion, AC, Utility Bag.



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- LED Worklight
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

General

| | |
|--------------------------|--|
| Application - For Use On | Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately) |
| Battery Type | 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Container Type | Vinyl Utility Bag |
| Crimp Force Capacity | 6 ton |
| Die Type | W Die and X Die |
| EU RoHS Indicator | Under Review |
| Power Source | 120V-AC Charger |
| Recharge Time | 0.5 h |
| Sub Brand | PATRIOT® IN-LINE® CRIMPER |
| Tool Type | Battery Actuated Scissor Action |
| Trade Name | PATRIOT® IN-LINE® |
| Type | Crimper and Cutter |
| UPC | 621945467323 |
| UPC 12 Digit | 621945467323 |

Dimensions

| | |
|------------|------------------------------|
| Dimensions | 18.73 in x 2.75 in x 4.38 in |
| Height | 4.38 in |
| Length | 18.73 in |
| Weight | 5.55 lb |
| Width | 2.75 in |

Electrical Ratings

| | |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | With Appropriate Jaw: Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8" |
|-----------------|---|

Logistics

| | |
|-----------------------|--|
| Carton Quantity | 1 |
| Minimum Pack Quantity | 1 |
| Package Contents | Tool, BG/D3 Crimp Jaw, (2) Batteries, Charger, Utility Bag |
| Pallet Quantity | 30 |

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PATMD-LW](#)
- [Sales Drawings - 50054521](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Video - BURNDY PATMD-LW](#)



A proud member of the Hubbell Family.

