



PATRIOT® IN-LINE® 82" F711 Pole Tool with Angled Head, ACSR Cut Jaw, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger

By Burndy
Catalog # [PATMDCUT82ALLIF](#)

PATMD-LW IN-LINE® 82" F711 Pole Tool with Angled Head, ACSR Cut Jaw, 3Ah Li-ion, AC.



Features

- Interchangeable scissor action crimping and cutting jaws available
- 355° Head rotation
- Uses W and X dies
- Safety trigger lock and locking jaw tabs
- Accepts 2.0Ah-6.0Ah 18V lithium-ion Makita batteries

Application

Crimping and Cutting

General

| | |
|--------------------------|--|
| Application - For Use On | Interchangeable Jaws: Crimp: ACSR, Aluminum, Copper Code/Flex; Cut: ACSR (26/7), Aluminum (AAC), Copper (Soft Drawn), EHS Guy Wire (sold separately) |
| Battery Type | 3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries) |
| Container Type | No Case/Bag |
| Crimp Force Capacity | 6 ton |
| Die Type | W Die and X Die |
| Power Source | 120V-AC Charger |
| Recharge Time | 0.5 h |
| Tool Type | Battery Actuated Scissor Action |
| Trade Name | PATRIOT® IN-LINE® |
| Type | Crimper and Cutter |
| UPC | 781810670231 |
| UPC 12 Digit | 781810670231 |

Dimensions

| | |
|-------------------------|-------------------------------|
| Dimension - Depth inch | 2.75 |
| Dimension - Height inch | 82 |
| Dimension - Width inch | 4.375 |
| Dimensions | 82.00 in x 4.375 in x 2.75 in |
| Height | 2.75 in |
| Length | 82.00 in |
| Weight | 13 lb |
| Width | 4.375 in |

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | With Appropriate Jaw: Crimping Capacity: Copper: #10 sol.-500 kcmil, Copper Flex: #8 AWG-350 kcmil, Aluminum: #14 sol.-350 kcmil, ACSR: #14 sol.-4/0 AWG; Cutting Capacity: ACSR (26/7) up to 556.5 kcmil, Aluminum (AAC) up to 636 kcmil, Copper (Soft Drawn) up to 600 kcmil, EHS Guy Wire up to 3/8" |
|-----------------|---|

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | UI |
|------------------------------------|----|

Logistics

| | |
|-----------------------|--|
| Carton Quantity | 1 |
| Minimum Pack Quantity | 1 |
| Package Contents | Tool, ACSR Cut Jaw, (2) Batteries, Charger |
| Pallet Quantity | 28 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50024918](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-PATMDCUT82ALLIF-SPEC-EN | REV 1/2024

