

Substation - Copper Bar Tap

By Burndy

Catalog # [QGFL26B1](#)

Copper Bartap, Cable to Drilled Bar, 8 AWG (Sol)-2/0 AWG (Str)
Cu Cable, 230 kV, Silicon Bronze H/W.



Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- 1-wrench installation

Application

Substation

General

Catalog Number	QGFL26B1
Connector Type	Bus Bar Clamp and Accessories
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810325100
UPC 12 Digit	7818103251000

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Height fraction	2-1/8 in
Dimension - Height inch	2.13 in
Dimension - Height mm	54.1 mm
Dimension - Width fraction	1-1/8 in
Dimension - Width inch	1.13 in
Dimension - Width mm	29 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1
-------------------------------	---

Conductor - Copper Solid Size Range	AWG;1/0 AWG;2/0 AWG 8 AWG-2/0 AWG
Conductor - Copper Str Size	#8 Sol;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;#2/0 Str
Conductor - Copper Str Size Range	#8 Sol-#2/0 Str
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_QGFL_LineArt](#)
- [Sales Drawings - SA045357](#)
- [Specifications - QGFL26B1](#)