

# QGFL29BIT6, Bartap, Cable to Flat, #6 Str-250 kcmil

By Burndy  
Catalog # [QGFL29BIT6](#)



Bartap, 6 Str. - 250 kcmil, Cable To Flat.

## Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- Can be installed side by side or in-line on NEMA drilled bar
- 1-wrench installation

## Application

Substation

## General

Catalog Number	QGFL29BIT6
Connector Type	Bus Bar Clamp and Accessories
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810005910
UPC 12 Digit	7818100059100

## Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.63 in
Dimension - Height fraction	3-1/8 in
Dimension - Height inch	3.13 in
Dimension - Height mm	79.5 mm
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.38 in
Dimension - Width mm	35 mm

## Conductor Related

Conductor - Copper Str Size	#6 Str;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	#6 Str-250 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[3D Models - QGFL29BIT6\\_MODEL-STEP](#)  
[3D Models - QGFL29BIT6\\_MODEL-PDF](#)  
[3D Models - QGFL29BIT6\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_QGFL\\_LineArt](#)  
[Sales Drawings - SA045357](#)  
[Specifications - QGFL29BIT6](#)