

QR4C, Heavy Duty Copper Splice Reducer

By Burndy
Catalog # [QR4C](#)



Splice or Reducer, 8 Str. - 4 Str., Recommended Tightening Torque: 110 IN-LB.

Features

- Type QR QIKLINK™ splice or reducer features a neat, compact, easy to tape installation
- One-wrench installation

General

Catalog Number	QR4C
Connector Type	In-Line
Installation Torque	110 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLINK™
UPC	781810334249

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Height fraction	13/16 in
Dimension - Height inch	0.81 in
Dimension - Height mm	19.1 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	5/8 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - Copper Solid Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size A Range	8 AWG-4 AWG
Conductor - Copper Solid Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG

Conductor - Copper Solid Size B Range	8 AWG-4 AWG
Conductor - Copper Str Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size A Range	8 AWG-4 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size B Range	8 AWG-4 AWG
Conductor Size	8-4 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • CU C Str-Size B • CU C Solid-Size A • CU C Solid-Size B

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	54
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_G4FQR_LineArt](#)
[Sales Drawings - SA011559-01](#)
[Specifications - QR4C](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QR4C-SPEC-EN | REV 10/2024