



## NAH4434N, 4-Hole Substation Cu Cable to Flat, 4/0 Str-1000 kcmil

By Burndy  
Catalog # [NAH4434N](#)

Cast Copper alloy terminal, 4/0 Str-1000 kcmil, 6.88 in Length, Cable to Pad.



### Application

Substation

### General

Catalog Number	NAH4434N
Clamping Element Design	Body and Cap
Connector Type	Terminal
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Sub Brand	SUBSTATION CONNECTOR
Type	NAH
UPC	781810002261
UPC 12 Digit	7818100022611

### Dimensions

Dimension - B Length fraction	2-22/25 in
Dimension - B Length inch	2.88 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2-31/50 in
Dimension - Height inch	2.62 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.12 in
Dimension - N inch	0.62 in
Dimension - Pad Size inch	3 x 3
Dimension - Pad Width inch	3.00 in
Dimension - Width fraction	2-81/100 in
Dimension - Width inch	2.88 in
Dimension - Width mm	73 mm

### Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	4/0 AWG-1000 kcmil
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>
Number of Conductors	1

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity 1

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_NAH\\_LineArt](#)  
[Sales Drawings - SE079584-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-NAH4434N-SPEC-EN | REV 8/2024