



PATRIOT® T3 Technology 15-Ton Battery Crimper, Latch Head, Uncovered, two 5.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT46T3LU05A2](#)



PAT46T3 Tech 15T Battery Crimper, Latch Head, Uncovered, 5Ah Li-Ion, AC, Hard Case.

Features

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- Light weight, latch head with 355° head rotation
- Uses P Dies and U Dies with PUADP1 Adapter
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46T3LU05A2
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Sub Brand	PATRIOT®
Tool Type	Battery Actuated Crimper, T3 Technology
Type	Crimper
UPC	621945625396

Dimensions

Dimensions	18.59 in x 3.26 in x 15.18 in
Height	15.18 in
Length	18.59 in
Weight	16 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

Product Assets

[Brochures - T3 Technology Trifold Brochure](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50110717](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT46T3LU05A2](#)
[Video - BURNDY T3 APP Features and Benefits](#)
[Video - BURNDY T3 APP Install & Register](#)
[Video - Introducing the PAT46T3](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-PAT46T3LU05A2-SPEC-EN | REV 3/2025