



# PATRIOT® 4-POINT® 6-Ton Dieless C-Head Battery Actuated Crimper, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag



By Burndy  
Catalog # [PAT4PC834L5PB](#)

PAT4PC834 4-POINT® 6T Dieless C-Head Battery Crimper, 5Ah Li-ion, AC, Nylon Pro Bag.

## Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

## Application

Crimping

## General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT4PC834L5PB
Container Type	Nylon Pro Bag
Crimp Force Capacity	6 ton
Die Type	Dieless
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	621945561953
UPC 12 Digit	621945561953

## Dimensions

Dimensions	15.62 in x 3.25 in x 14.10 in
Height	14.1 in
Length	15.62 in
Weight	12.5 lb
Width	3.25 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

### Crimping Ranges

Copper Terminals: #8-1000 kcmil  
 Copper Splices: #8-500 kcmil  
 Copper Flex Terminals: #8-777.7 Flex  
 Copper Flex Splices: #8-500 kcmil  
 Aluminum Terminals: #8-750 kcmil  
 Aluminum Splices: #8-350 kcmil\*  
 \*1.06" barrel diameter maximum for aluminum splices due to jaw opening  
 Aluminum HYPLUG™: #8-750 kcmil

## Certifications And Compliance

Buy American Compliant	No
UL Listed	No

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Nylon Pro Bag
Pallet Quantity	12

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50106125](#)
- [SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
- [Specifications - PAT4PC834L5PB](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-PAT4PC834L5PB-SPEC-EN | REV 10/2024