



PATRIOT® 2156 Series Latch Head Battery Cutter, (2) 5.0Ah 18V Li-ion Batteries, 120V-AC Charger, Nylon Pro Bag

By Burndy
Catalog # [PATCUT2156L5PB](#)



PATCUT2156 Latch Head Battery Cutter, 5Ah Li-ion, AC, Nylon Pro Bag.

Features

- 180° head rotation
- Durable hardened steel blades
- Specialized latch head for mid-span cuts
- Mechanical ram release with no power consumption

Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Battery Type	5.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PATCUT2156L5PB
Container Type	Nylon Pro Bag
Crimp Force Capacity	10 ton
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.75 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945562257
UPC 12 Digit	621945562257

Dimensions

Dimensions	16.46 in x 3.27 in x 13.66 in
Height	13.66 in
Length	16.46 in
Weight	14.1 lb

Width 3.27 in

Electrical Ratings

Operating Voltage 18 VDC

Conductor Related

Crimping Ranges Cutting Capacity:
Copper/Aluminum up to 2.0";
ACSR up to 2156 kcmil; Ground
Rod up to 3/4"; Rebar up to
5/8"; Soft Steel Bolts up to
3/4"; Standard Guy up to 9/16";
EHS Guy Strand up to 9/16"

Certifications And Compliance

Buy American Compliant No
UL Listed No

Logistics

Carton Quantity 1
Minimum Pack Quantity 1
Package Contents Cutter, (2) Batteries, Charger,
Lanyard, Nylon Pro Bag
Pallet Quantity 12

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50106125](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PATCUT2156L5PB](#)

