



PATRIOT® IN-LINE® 6-Ton Scissor Action, Crimper Jaw with Permanent O & D3 Grooves (Jaw Only)

By Burndy
Catalog # [PATMD68LWJAW](#)



PATMD-LW IN-LINE® 6T Scissor Action, Crimper Jaw with Permanent O & D3 Grooves (Jaw Only).

Features

- Crimp jaw with permanent O/D3 grooves
- Interchangeable scissor action jaw
- Locking jaw tabs
- Uses W and X dies
- for PATMD-LW series batteries

Application

Crimping and Cutting

General

| | |
|--------------------------|--|
| Application - For Use On | Crimping with Permanent O/D3 Die Grooves, W & X Dies |
| Catalog Number | PATMD68LWJAW |
| Crimp Force Capacity | 6 ton |
| Die Type | W Die and X Die |
| EU RoHS Indicator | Contact Manufacturer |
| Tool Type | Crimper Jaw |
| Trade Name | PATRIOT® IN-LINE® |
| Type | Crimper and Cutter |
| UPC | 621945483484 |
| UPC 12 Digit | 621945483484 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 5.06 in x 4.27 in x 1.0625 in |
| Height | 1.0625 in |
| Length | 5.06 in |

| | |
|--------|---------|
| Weight | 2 lb |
| Width | 4.27 in |

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | Copper: #10 sol. - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum: #14 sol. - 350 kcmil, ACSR: #14 sol. - 4/0 AWG |
|-----------------|---|

Certifications And Compliance

| | |
|------------------------|----------------------|
| Buy American Compliant | Contact Manufacturer |
|------------------------|----------------------|

Logistics

| | |
|-----------------------|------------------------------------|
| Minimum Pack Quantity | 1 |
| Package Contents | O/D3 Crimper Jaw for PATMD-LW Tool |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_PATMD-LW](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50054529](#)
- [Specifications - PATMD68LWJAW](#)
- [Video - BURNDY PATMD-LW](#)

