



PATRIOT® Combo Kit: PAT444S 11-Ton Dieless C-Head Crimper, PATCUT1500 CU/AL Cutter, (2) 3.0Ah 18V Li-ion Bat, AC Chg, (2) Lanyards, HD Hard Case

By Burndy
Catalog # PATRIOTKIT2



PATRIOT® Combo Kit: PAT444S 11-Ton Dieless C-Head Crimper, PATCUT1500 CU/AL Cutter, 3Ah Li-ion, AC, Lanyards, HD Hard Case

Features

- CRIMPER: C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al, #4 - 556.5 ACSR, ACAR, AAC, AAAC
- 355° Head rotation
- 11 ton output force
- Ergonomically balanced tool design
- CUTTER: Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- TOOLS: Accept 2Ah-6Ah 18V Makita lithium-ion batteries
- KIT: Packed in a heavy duty hardcase with custom foam and secure latches.

Application

Crimping and Cutting

General

Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	11 ton
Die Type	Dieless
EU RoHS Indicator	Contact Manufacturer
Power Source	120V-AC Charger
Recharge Time	0.5 h
Sub Brand	PATRIOT® Crimper & Cutter
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimper and Cutter
UPC	621945560932
UPC 12 Digit	621945560932

Dimensions

Dimensions	24.53 in x 19.55 in x 9.9 in
Height	9.9 in
Length	24.53 in
Weight	43 lb
Width	19.55 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping: Copper: #4 AWG - 1000 kcmil; Aluminum: #4 AWG - 1000 kcmil; ACSR: #4 AWG - 556.5 kcmil; Cutting: Aluminum: 1500 kcmil; Copper (Soft Drawn): 1000 kcmil
-----------------	--

Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Crimper, Cutter, (2) Batteries, Charger, (2) Lanyards, Heavy Duty Hard Case

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50101566](#)
- [SDS - Burndy BAT18VLI SDS Sheet](#)
- [Video - PATCUT1500 Series Cutter](#)
- [Video - The New PAT444S Dieless Tool](#)





A proud member of the Hubbell Family.

BRDY-PATRIOTKIT2-SPEC-EN | REV 10/2023