

## Q2A282NTN, Two Conductor Two Hole Mounting Heavy Duty Copper Lug Connector, 3/0-4/0 AWG Str, 1/2" Stud, 1-3/4" Spacing, 2 Screws, Tin Plated



By Burndy  
Catalog # [Q2A282NTN](#)

Cast Cu Alloy QIKLUG Terminals, 2 Cables To Pad/Bar, 2-Nema Holes, 3/0 - 4/0 Str. Cu, Tin Plated.

### General

Catalog Number	Q2A282NTN
Connector Type	Duel Clamp
Installation Torque	250 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type Plated	Hexagonal Bolt Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810135570
UPC 12 Digit	7818101355700

### Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.09 in
Dimension - F Width Center to Center inch	0.69 in
Dimension - Height fraction	1-3/8 in
Dimension - Height inch	1.31 in
Dimension - Height mm	35.1 mm
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.31 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	2.12 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	2.12 in

Dimension - Width mm 54 mm

### Electrical Ratings

Rating - Minimum Voltage 600

### Conductor Related

Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Size	3/0-4/0 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	2310

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd..023314-01](#)  
[Specifications - Q2A282NTN](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-Q2A282NTN-SPEC-EN | REV 10/2024