



# QGFL26B2T6, Cu Bartap, Cu Cable to Drilled Bar, #8 AWG Sol-2/0 AWG Str Cu, Silicon Bronze Hardware



By Burndy  
Catalog # [QGFL26B2T6](#)

Copper Bartap, Cable to Drilled Bar, 8 AWG (Sol)-2/0 AWG (Str)  
Cu Cable, 230 kV, Silicon Bronze H/W,1.1/8 W,2-40/50 H.

## Features

- High copper alloy BARTAP™ for joining a range of cable to bar or pad
- Can be installed side by side or in-line on NEMA drilled bar
- 1-wrench installation

## Application

Substation

## General

Catalog Number	QGFL26B2T6
Connector Type	Bus Bar Clamp and Accessories
EU RoHS Indicator	Yes
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810005828
UPC 12 Digit	7818100058288

## Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Height fraction	2-40/50 in
Dimension - Height inch	2.88 in
Dimension - Height mm	73.2 mm
Dimension - Width fraction	1-1/8 in
Dimension - Width inch	1.13 in
Dimension - Width mm	29 mm

## Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
-------------------------------	---

Conductor - Copper Solid Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size	#8 Sol;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;#2/0 Str
Conductor - Copper Str Size Range	#8 Sol-#2/0 Str
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - QGFL26B2T6\\_MODEL-IGES](#)
- [3D Models - QGFL26B2T6\\_MODEL-STEP](#)
- [3D Models - QGFL26B2T6\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_QGFL\\_LineArt](#)
- [Sales Drawings - SA045357](#)
- [Specifications - QGFL26B2T6](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-QGFL26B2T6-SPEC-EN | REV 10/2024