



## QPX282C, Heavy Duty Copper Tapping Connector, Run: 1-4/0, Tap: 6-2 AWG

By Burndy  
Catalog # [QPX282C](#)

VERSITAP™ Mechanical Parallel Clamp for Copper;  
Accommodates: Run: #1 - 4/0 AWG; Tap: #6 - #2 AWG



### Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

### Application

For Tee, Cross, Parallel, Butt And Tap Connections, Copper

### General

Catalog Number	QPX282C
Connector Type	Universal Clamp
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	VERSITAP
Temperature Rating	194
Trade Name	VERSITAP™
Type	QPX
UPC	781810342008
UPC 12 Digit	7818103420088

### Dimensions

Dimension - Height fraction	2-1/16
Dimension - Height inch	2.06
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Width fraction	1-9/16 in
Dimension - Width inch	1.56
Dimension - Width mm	40 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	1 AWG-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Run</li><li>• CU C Str-Tap</li></ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_QPX\\_PARA\\_CLAMP\\_LineArt](#)  
[Sales Drawings - sa007887-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-QPX282C-SPEC-EN | REV 6/2024