



QPX442C, Heavy Duty Copper Tapping Connector, Run: 500-1000 kcmil; Tap: #6-#2 AWG

By Burndy
Catalog # [QPX442C](#)



VERSITAP™ Mechanical Parallel Clamp for Copper;
Accommodates: Run: 500 - 1000 kcmil; Tap: #6 - #2 AWG.

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

General

Catalog Number	QPX442C
Connector Type	Universal Clamp
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810344750
UPC 12 Digit	7818103447500

Dimensions

Dimension - Height fraction	2-11/16
Dimension - Height inch	2.69
Dimension - Height mm	66.8 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.22
Dimension - Width mm	57 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil-1000 kcmil
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_QPX_PARA_CLAMP_LineArt](#)
- [Sales Drawings - sa007887-01](#)
- [Specifications - QPX442C](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-QPX442C-SPEC-EN | REV 10/2024