

Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # T1010



Copper Compression Terminal, Ring Tongue, 12-10 AWG, #8-#10 Stud, Long Barrel, Tin Plated.

Features

- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

General

Color	
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Standard
Listings	UL, CSA
Material	Carbon Steel
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722084
UPC 12 Digit	7818107220844

Dimensions

Depth	15
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Diameter Max Size inch	0.12 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.2 in
Dimension - L Length Overall mm	21
Dimension - Length Overall inch	0.82
Dimension - Pad Width inch	0.38 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8 - #10
Dimension - Z (inch)	0.29 in
Height	11 in
Width	13 in

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[3D Models - T1010_MODEL-STEP](#)

3D Models - T1010_MODEL-STEP
3D Models - T1010_MODEL-IGES
3D Models - T1010_MODEL-PDF
Catalogs - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Sales Drawings - 50094154



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-T1010-SPEC-EN | REV 5/2024