



TP1610, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # [TP1610](#)

Copper Terminal, Ring Tongue, 22-16 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated.



Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP1610
Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810714843
UPC 12 Digit	7818107148433

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.26 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Solid Size	20 ;18 AWG;17 AWG;16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_TP1010_LineArt](#)
[Sales Drawings - 50093722](#)
[Specifications - TP1610](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-TP1610-SPEC-EN | REV 8/2024