

TP162Z, Vinyl Flanged Fork Terminal For 22 - 16 AWG

By Burndy
Catalog # TP162Z



Vinyl Flanged Fork Terminal For 22 - 16 AWG.

Features

- Flange fork tongue design allows fast installation as screw only has to be loosened for termination
- The flanges on the end of the fork terminal aid in preventing a slightly loose terminal from becoming fully disconnected from the screw
- Flanges make re-securing a loose terminal easier

Application

For Fast Installation And Security

General

Catalog Number	TP162Z
Color Code	Red
Connector Type	Flanged Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Flanged Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Flange Fork
UPC	781810714201
UPC 12 Digit	7818107142011

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	#2
Dimension - Hole Size fraction	8/89
Dimension - Hole Size inch	0.09 in
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in

Dimension - Pad Width inch	0.17 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#2
Dimension - Z (inch)	0.23 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#20 AWG to #22 AWG; 16 AWG to 18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_TP1410Z_LineArt](#)
- [Sales Drawings - 50094185](#)
- [Specifications - TP162Z](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-TP162Z-SPEC-EN | REV 10/2024