

UH175, Substation Copper Bus Support, 1-1/2" IPS, 5" Bolt Dia, 1/2" Bolt

By Burndy
Catalog # UH175



Cast Cu Alloy Bus Support, 1-1/2" IPS, 5" Bolt Dia, 1/2" Bolt.

Application

Substation

General

Catalog Number	UH175
Connector Type	Bus Support
Fitting Type	Slip or Rigid
Hardware Type	Cap mounting kit (w/o nuts)
Installation Torque	480 in-lb
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Mounting Hardware	5/8-11 x 1" LG
One Wrench Installation	Y
Plated	N
Plating Type	Unplated
Type	Cable or Tube to Insulator Bus Supports
UPC	781810004524
UPC 12 Digit	7818100045244

Dimensions

Bolt Circle Diameter	5 in
Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - G inch	2.50 in
Dimension - Height fraction	3-7/8 in
Dimension - Height inch	3.88 in
Dimension - Height mm	99 mm
Dimension - Hole Size fraction	11/16
Dimension - Hole Size inch	0.69 in
Dimension - Width fraction	4 in
Dimension - Width inch	4.00 in
Dimension - Width mm	102 mm

Conductor Related

Conductor - Connection Combination	Base to Tube
Conductor - Copper Tube EH Size	1 1/2 IPS
Conductor - Copper Tube EH Size Range	1 1/2 IPS
Conductor - Copper Tube Std Size	1 1/2 IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS
Conductor Type	<ul style="list-style-type: none"> • CU Tube Std-Size • CU Tube EH-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

- [3D Models - UH175_MODEL-PDF](#)
- [3D Models - UH175_MODEL-STEP](#)
- [3D Models - UH175_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section L - Bolted Substation](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UH_LineArt](#)
- [Sales Drawings - sa007374-01](#)
- [Specifications - UH175](#)