

UC25R2RS, Aluminum Clamp

By Burndy

Catalog # [UC25R2RS](#)



High strength, high conductivity aluminum alloy. Properly proportioned to minimize stress corrosion and deterioration by galvanic action, Wrench: 1/2.

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201 And 5005

General

Catalog Number	UC25R2RS
EU RoHS Indicator	Yes
Installation Torque	180 in-lb
Recommended in-lb	
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Sub Brand	TAPIT
Trade Name	TAPIT™
Type	UC-RS
UPC	781810093009
UPC 12 Digit	7818100930099

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.125 in
Dimension - Height fraction	1-5/8 in
Dimension - Height inch	1.68 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.47 in
Dimension - Width mm	37 mm

Conductor Related

Conductor - AAAC 5005 Size A	6 AWG-1/0 AWG Range
Conductor - AAAC 5005 Size B	6 AWG-1/0 AWG Range
Conductor - AAAC 6201 Size A	6 AWG-1/0 AWG Range
Conductor - AAAC 6201 Size B	6 AWG-1/0 AWG Range
Conductor - AL Str Size A	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size A Range	8 AWG-1/0 AWG
Conductor - AL Str Size B	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size B Range	8 AWG-2 AWG
Conductor - Copper Solid Size A	8 AWG
Conductor - Copper Solid Size A Range	8 AWG
Conductor - Copper Solid Size B	8 AWG
Conductor - Copper Solid Size B Range	8 AWG
Conductor - Copper Str Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size A Range	8 AWG-1/0 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size B Range	8 AWG-2 AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity 25

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_UC-RS_LineArt](#)
[Sales Drawings - SD..057342-01](#)
[Specifications - UC25R2RS](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-UC25R2RS-SPEC-EN | REV 8/2024