



UCT26RSSS, Aluminum Parallel Groove Clamp featuring LINEMAN ASSIST

By Burndy
Catalog # [UCT26RSSS](#)

Aluminum Parallel Groove Clamp, Run: Cu & AL: 8 Sol. - 2/0, ACSR: 6 - 2/0, Tap: Cu & AL: 6 Sol. - 2/0, ACSR: 6 - 2/0, Stainless hardware.



Application

The system helps secure both the Tap and Run conductors while installing on primary, secondary and service lines. Connector is not recommended for Copper to Copper applications

General

EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	FASTAP
Trade Name	FASTAP™
Type	UCT
UPC	781810643808
UPC 12 Digit	7818106438088

Dimensions

Bolt Size	3/8"-16
Dimension - Height inch	2.62 in
Dimension - Length Overall inch	1.62 in
Dimension - Width inch	2.50 in

Conductor Related

Conductor - AAAC 5005 Size	6 STR - 2/0 STR
Conductor - AAAC 5005 Size Range	6 STR - 2/0 STR
Conductor - AAAC 6201 Size	6 STR - 2/0 STR
Conductor - AAAC 6201 Size Range	6 STR - 2/0 STR
Conductor - ACSR Str Size	6 STR - 2/0 STR
Conductor - ACSR Str Size A Range	6 Str. - 2/0
Conductor - ACSR Str Size B Range	6 Str. - 2/0
Conductor - AL Str Size A	8 SOL - 2/0 STR
Conductor - AL Str Size A Range	8 Sol. 2/0
Conductor - AL Str Size B	8 SOL - 2/0 STR
Conductor - AL Str Size B Range	8 Sol. - 2/0 Str.
Conductor - Copper Solid Size	#8 - 2/0
Conductor - Copper Solid Size Range	#8 - 2/0
Conductor - Copper Str Size A Range	8 Sol. 2/0
Conductor - Copper Str Size B Range	8 Sol. - 2/0 Str.

Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size A • AL C Str-Size B • CU C Solid-Size • CU C Str-Size A • CU C Str-Size B • CU Weld C Solid-Size
----------------	--

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-UCT26RSSS-SPEC-EN | REV 5/2024