

WCB28, WEJTAP Connector

By Burndy
Catalog # [WCB28](#)



Wejtap connector installed with blue booster, .532-.650 (Run), .525-.650 (Tap).

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCB28
Connector Type	Tap
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873359
UPC 12 Digit	7818108733599

Dimensions

Dimension - F Width Center to Center inch	1.89 in
Dimension - G inch	1.05 in

Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7)

Minorca kcmil;134.6 (12/7)
Leghorn kcmil;159 (12/7)
Guinea kcmil;176.9 (12/7)
Dotterel kcmil;190.8 (12/7)
Dorking kcmil;211.3 (12/7)
Cochin kcmil;203.2 (16/9)
Brahma kcmil;266.8 (18/1)
Waxwing kcmil;266.8 (26/7)
Owl kcmil;266.8 (26/7)
Partridge kcmil
4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
250 kcmil;266 kcmil;300 kcmil
250 kcmil-300 kcmil
4/0 AWG;250 kcmil;266 kcmil;300 kcmil
4/0 AWG-300 kcmil

Conductor - ACSR Str Tap Range

Conductor - AL Str Run

Conductor - AL Str Run Range

Conductor - AL Str Tap

Conductor - AL Str Tap Range

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCB_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCB28](#)