

## WCB43, WEJTAP Connector

By Burndy  
Catalog # [WCB43](#)



Wejtap connector installed with blue booster, .600-.684 (Run), .324-.500 (Tap).

### Features

WEJTAP Connector installed with Blue Power Booster

### Application

For use in tap applications using large run and tap conductor sizes

### General

|                   |                  |
|-------------------|------------------|
| Catalog Number    | WCB43            |
| Connector Type    | Tap              |
| EU RoHS Indicator | Yes              |
| Material          | Aluminum         |
| Sub Brand         | WEJTAP           |
| Trade Name        | WEJTAP™          |
| Type              | Wejtap Connector |
| UPC               | 781810873557     |
| UPC 12 Digit      | 7818108735577    |

### Dimensions

|   |        |
|---|--------|
| Dimension - F Width Center to Center inch | 2 in   |
| Dimension - G inch                        | 1.1 in |

### Conductor Related

|                                |   |
|--------------------------------|---|
| Conductor - ACSR Str Run       | 266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil |
| Conductor - ACSR Str Run Range | 266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil  |

|                                |                                       |
|--------------------------------|---------------------------------------|
| Conductor - ACSR Str Tap       | 1 (6/1) Robin AWG;1/0 (6/1) Raven AWG |
| Conductor - ACSR Str Tap Range | 1 (6/1) Robin AWG-1/0 (6/1) Raven AWG |
| Conductor - AL Str Run         | 300 kcmil;336 kcmil;350 kcmil         |
| Conductor - AL Str Run Range   | 300 kcmil-350 kcmil                   |
| Conductor - AL Str Tap         | 1 AWG;1/0 AWG;2/0 AWG;3/0 AWG         |
| Conductor - AL Str Tap Range   | 1 AWG-3/0 AWG                         |

### Certifications And Compliance

|                               |    |
|-------------------------------|----|
| Buy American Compliant        | No |
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| UL Listed                     | No |

### Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)  
[Customer Notices - Prop 65 Notice](#)  
[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_WCB\\_Lineart](#)  
[Sales Drawings - 50008861](#)  
[Specifications - WCB43](#)