

UW2R, Parallel Groove Clamp, Aluminum Casting

By Burndy
Catalog # UW2R



High Strength Aluminium Casting With Galvanized Steel U-Bolts.

General

Catalog Number	UW2R
Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Oxide Inhibitor Type	Penetrox A
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	CLIPIT™
UPC	781810107003

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - Height fraction	2-5/8 in
Dimension - Height inch	2.58 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.82 in
Dimension - Width mm	46 mm

Conductor Related

Conductor - AAAC 5005 Run	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Run	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil

Conductor - ACSR Str Run	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - AL Str Run	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_UWR_CLIPIT_LineArt](#)
[Sales Drawings - sc039787-01](#)



A Hubbell brand