

# WCY100, WEJTAP Connector

By Burndy  
Catalog # [WCY100](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 0.351 - 0.257 (Tap),  
Installed With Yellow Booster.

## General

Catalog Number	WCY100
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810876404
UPC 12 Digit	7818108764044

## Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.96 in

## Conductor Related

Conductor - ACSR Str Run	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil;715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil;900 (54/7) Canary kcmil;954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil

Conductor - ACSR Str Tap	4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG
Conductor - ACSR Str Tap Range	4 (7/1) Swanate AWG-1 (6/1) Robin AWG
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil;1033 kcmil;1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil
Conductor - AL Str Run Range	600 kcmil-1200 kcmil
Conductor - AL Str Tap	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - AL Str Tap Range	4 AWG-1 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_WCY\\_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCY100](#)