

## WCY112PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY112PB](#)



WEJTAP Connector, 1.302 - 1.242 (Run), 0.742 - 0.642 (Tap),  
With Yellow Power Booster Assembly.

### General

Catalog Number	WCY112PB
Color	Yellow
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810036747
UPC 12 Digit	7818100367477

### Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

### Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Tap	266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Tap Range	266.8 (26/7) Partridge kcmil-397.5 (18/1) Chickadee kcmil

Conductor - AL Str Run	1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil;1300 kcmil
Conductor - AL Str Run Range	1100 kcmil-1300 kcmil
Conductor - AL Str Tap	300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Tap Range	300 kcmil-400 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>ACSR C Str-Run</li> <li>AL C Str-Run</li> <li>ACSR C Str-Tap</li> <li>AL C Str-Tap</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_WEJTAP\\_POWER\\_LUG\\_LineArt](#)  
[Sales Drawings - 50014998](#)  
[SDS - WEJTAP Power Booster SDS](#)  
[Specifications - WCY112PB](#)